









SCHEMATIC	1
	3
	2
Model	DC-026M
Center Pin	Ø2.0 mm
	Ø2.5 mm



	MATERIAL	PLATING
axle sleeve	Brass	tin
plastic	Pbt	
center pin	Brass	tin
terminal 1	Brass	tin
terminal 2	Brass	tin
terminal 3	Phosphor Bronze	tin

						DSND		DATE		SCALE: N/A	MODEL TYPE: DC POWER JACK
△X						ANGLAR	±5°	DWN		VIEW:	PART NO.:
△X						X.X	±0.2mm	CHKD		UNIT: mm	
△X						X.XX	±0.1mm	APPD		SIZE: A4	DWG NO.: DC-026M-5A-2.0
MARK	DESCRIPTION	DATE	REVISED	APPROVED		X.XXX	±0.05mm				
REVISIONS						UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT 1.0g
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn											SHEET 1/1
											REVISION A0