



P. C. B LAYOUT TOP VIEW

|            |         |
|------------|---------|
| SCHEMATIC  |         |
| Model      | DC-044B |
| Center Pin | Ø2.0 mm |
|            | Ø2.5 mm |

|              | MATERIAL        | PLATING |
|--------------|-----------------|---------|
| axis support | Brass           | silver  |
| center pin   | Brass           | silver  |
| plastic      | Pbt             |         |
| terminal 1   | Brass           | silver  |
| terminal 2   | Phosphor Bronze | silver  |
| terminal 3   | Brass           | silver  |

|                                               |             |      |         |          |                        |         |      |  |                                       |                              |          |  |
|-----------------------------------------------|-------------|------|---------|----------|------------------------|---------|------|--|---------------------------------------|------------------------------|----------|--|
|                                               |             |      |         |          | DSND                   |         | DATE |  | SCALE: N/A                            | MODEL TYPE:<br>DC POWER JACK |          |  |
|                                               |             |      |         |          | ANGLAR                 | ±5°     | DWN  |  | VIEW:                                 | PART NO.:                    |          |  |
|                                               |             |      |         |          | X.X                    | ±0.2mm  | CHKD |  | UNIT: mm                              | DWG NO.:<br>DC-044B-3A-2.5   |          |  |
|                                               |             |      |         |          | X.XX                   | ±0.1mm  | APPD |  | SIZE: A4                              |                              |          |  |
|                                               |             |      |         |          | X.XXX                  | ±0.05mm |      |  |                                       |                              |          |  |
| MARK                                          | DESCRIPTION | DATE | REVISED | APPROVED | UNSPECIFIED TOLERANCES |         |      |  | XKB INDUSTRIAL PRECISION CO., LIMITED |                              |          |  |
| REVISIONS                                     |             |      |         |          |                        |         |      |  | WEIGHT                                | SHEET                        | REVISION |  |
| www.xk-dg.cn www.helloxkb.com www.helloxkb.cn |             |      |         |          |                        |         |      |  | 1.0g                                  | 1/1                          | A0       |  |