



SPECIFICATION

1. Rating : DC 20V 7A;
2. Contact resistance: $\leq 0.03 \Omega$;
3. Insulation resistance: $\geq 100M \Omega$ (DC250V);
4. Withstand voltage: 500VAC ;
5. Insertion and extraction force: 5-30N;
6. life test: 5,000 cycles.
7. PLUG 插入后上下左右4个方向无瞬断现象。

	MATERIAL	PLATING
center pin	Brass	tin
coat	Sus	
terminal 1	Phosphor Bronze	tin
terminal 2	Phosphor Bronze	tin
terminal 3	Phosphor Bronze	tin
plastic	Pa9t	

DSND		DATE		SCALE: N/A	MODEL TYPE: DC POWER JACK
DWN		DATE		VIEW:	PART NO.:
CHKD		DATE		UNIT: mm	DWG NO.:
APPD		DATE		SIZE: A4	DC-C024E-7A-1.65
UNSPECIFIED TOLERANCES					WEIGHT
XKB INDUSTRIAL PRECISION CO.,LIMITED					1.0g
					SHEET
					1/1
					REVISION
					A0

MARK	DESCRIPTION	DATE	REVISED	APPROVED	REVISIONS
△X					
△X					
△X					

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn

ANGLAR $\pm 5^\circ$
 X.X $\pm 0.2mm$
 X.XX $\pm 0.1mm$
 X.XXX $\pm 0.05mm$