



P. C. B LAYOUT TOP VIEW

SWITCH CONNECTOR

SCHEMATIC	
Model	DC-044D-2.5A
Center Pin	Ø2.0 mm
	Ø2.5 mm

	MATERIAL	PLATING
center pin	Brass	tin
terminal 1	Brass	tin
terminal 2	Phosphor Bronze	tin
terminal 3	Brass	tin
plastic	Pbt	

DSND		DATE		SCALE: N/A	MODEL TYPE: DC POWER JACK		
DWN		DATE		VIEW:	PART NO.:		
CHKD		DATE		UNIT: mm	DWG NO.:		
APPD		DATE		SIZE: A4	DC-044D-2.5A-2.0-SMT		
UNSPECIFIED TOLERANCES					WEIGHT	SHEET	REVISION
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn					1.0g	1/1	A0

XKB INDUSTRIAL PRECISION CO., LIMITED