








NOTE:
Rating: DC 12V 50mA
Operating Force: 200±100gf
Lifetime: 10,000 Cycles



P.C.B LAND PATTERN

PAPT NO	L	Color
SS-3292S-L1	1.5	B:black W:white
SS-3292S-L2	2.0	
SS-3292S-L3	3.0	

ITEM	PAPT NAME	TER,NO	QTY	MATERIAL	FINISHING	REMARK
⑤	Terminal	—	7	Brass (0.30t)	ag Plated	—
④	Contact spring	—	1	Phosphor branze	ag Plated	—
③	Base	—	1	Lcp	Black	—
②	Cover	—	1	Sus	Natural	—
①	Keystake	—	1	Pa46	Black	—

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
△X					ANGLAR ±5°
△X					X.X ±0.2mm
△X					X.XX ±0.1mm
△X					X.XXX ±0.05mm

DSND		DATE		SCALE: N/A	MODEL TYPE: SLIDE SWITCH
DWN		DATE		VIEW:	PART NO.:
CHKD		DATE		UNIT: mm	DWG NO.: SS-3292S-X-X
APPD		DATE		SIZE: A4	
XKB INDUSTRIAL PRECISION CO.,LIMITED				WEIGHT 1.0g	SHEET 1/1
					REVISION A0