



Code-X	H	Code-X	H
A	4.3	O	11.0
B	4.5	P	11.5
C	5.0	Q	12
D	5.5	R	12.5
E	6.0	S	13.0
F	6.5	T	13.5
G	7.0	U	14.0
H	7.5	V	15.0
I	8.0	W	15.5
J	8.5	X	16
K	9.0	Y	16.5
L	9.5	Z	17
M	10.0		
N	10.5		

SPECIFICATION

Contact Rating 50mA, 12V DC
 Contact Resistance 100mΩ max.
 Insulation Resistance 100MΩ min. 500V DC
 Dielectric Strength 250V A⁻ 1ite
 Travel 0.20mm
 Operating Temp. -25°C ~ +70°C
 Storage Temp. -30°C ~ +80°C

PAPT NO	TC-1102DE-X-X
Operating Force	A: 100gf B: 160gf C: 260gf
Height	Code-X

⑤ Terminal	3	Brass (0.30t)	ag Plated
④ Contact	1	F.ag/SUS	
③ Base	1	PPA	
② Cover	1	Brass	Tin plated
① Keystake	1	PPA	

MODEL TYPE: TACT SWITCH

PART NO.:

UNIT: mm

DWG NO.: TC-1102DE-X-X

WEIGHT SHEET REVISION
 1/0g 1/1 A0

DSND	DATE	SCALE: N/A
DWN	DATE <td>VIEW: </td>	VIEW:
CHKD	DATE <td>PART NO.:</td>	PART NO.:
APPD	DATE <td>SIZE: A4</td>	SIZE: A4

UNITS: mm	tolerance:	UNSPECIFIED TOLERANCES
X.X	±0.2mm	
X.XX	±0.1mm	
X.XXX	±0.05mm	

REVISIONS	DATE	REVISED	APPROVED
ΔX			
ΔX			
ΔX			
MARK			

DESCRIPTION

www.kk-dg.cn www.hellokxb.com www.hellokko.cn

XKB INDUSTRIAL PRECISION CO., LIMITED