



SK-13D07-X-X-X-X

Knob Type	H (mm)	COLOUR
L	2 ~ 12	B.Black
G		R.Red
V		

G TYPE	L TYPE	V TYPE

RATING	0.3A 50V DC	
CIRCUIT	1P2T	
CONTACT RESISTANCE	100m	MAX.
TRAVEL	2mm	
OPERATING FORCE	250±100gf	
OPERATING LIFE(cycles)	10,000	

ITEM	PAPT NAME	TER.NO	QTY	MATERIAL	FINISHING	REMARK
④	Terminal	—	4	Brass (0.30t)	ag Plated	
③	Base	—	1	Phenolic Resin		
②	Cover	—	1	Sus	Natural	
①	Keystake	—	1	Pa66	Black	

DSND	DATE	SCALE: N/A	MODEL TYPE:
DWN	DATE	VIEW:	SLIDE SWITCH
CHKD	DATE	UNIT: mm	PART NO.: SK-13D07
APPD	DATE	SIZE: A4	DWG NO.: SK-13D07-X-X

REVISIONS	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					ANGULAR ±6°
ΔX					L ≤ 4 ±0.2
ΔX					4 < L ≤ 16 ±0.3
MARK					16 < L ≤ 63 ±0.4
					L > 63 ±0.5

XKB INDUSTRIAL PRECISION CO., LIMITED			
WEIGHT	SHEET	REVISION	
1.0g	1/1	A0	