





④	Terminal	6	Brass (0.30t)	ag Plated					
③	Base	1	Phenolic Resin						
②	Cover	1	Sus	Natural					
①	Keystake	1	Pa66	Black					
ITEM	PART NAME	TER.NO	QTY	MATERIAL	FINISHING	REMARK			

RATING	0.3A 50V DC
CIRCUIT	1P2T
CONTACT RESISTANCE	100m MAX.
TRAVEL	2mm
OPERATING FORCE	250±100gf
OPERATING LIFE(cycles)	10,000

						DSND		SCALE: N/A	MODEL TYPE: SLIDE SWITCH
ΔX						DWN		VIEW:	PART NO.: SK-14D07
ΔX						CHKD		UNIT: mm	DWG NO.: SK-14D07-X-X
ΔX						APPD		SIZE: A4	
MARK									
DESCRIPTION						DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
REVISIONS						DATE	REVISED	APPROVED	
www.xk-dg.cn www.1k0k.com www.1k0k.cn						XKB INDUSTRIAL PRECISION CO.,LIMITED			
						WEIGHT	SHEET	REVISION	
						1.0g	1/1	A0	