





FREE	LOCK
1 ○	1 ○
2 ○	2 ○
3 ○	3 ○
4 ○	4 ○
5 ○	5 ○
6 ○	6 ○

SPECIFICATION	
1.环境温度(Operating Temp)	-20℃~+80℃
2.相对湿度(Working Humidity)	5%~35%
3.额定规格(Rated Value)	DC50V/30mA
4.接触电阻(Contact Resistance)	100mΩ max
5.绝缘电阻(Insulation Resistance)	100MΩ min
6.耐电压(Withstand Voltage)	250Vac/60S
7.动作力(Operating Force)	250±50gf
8.使用寿命(Operating Life)	100,000 cycle


FREE	9.1
LOCK	8.2



View A



PCB LAYOUT



view A  
scale 1:1

7	Crochet Hook	1PCS	Carbon Steel
6	Spring	1PCS	Carbon Steel
5	Contact Chip	2PCS	Silver-Coated Copper
4	Terminals	6PCS	Copper plated Silver
3	Panel	1PCS	LCP Natural Color
2	Keypad	1PCS	LCP Black
1	Housing	1PCS	LCP Black
序号 NO.	零件名称 PART NAME	数量 QTY	材质 MATERIAL

**东莞市美韩电子科技有限公司**  
Dongguan Usakro Electronic Technology Co., Ltd.

普通公差 common tolerance		角度angular: ±0.5°	
0~5±0.15;	5~10±0.3;	10~30±0.5;	
DATE	2018-7-18	SCALE	free
CHECKED	JEFF	核 准 APPROVED	JEFF
DRAWN	JEFF	单 位 UNIT	mm
品名Title	7x7平头自锁开关	料号Part NO.	UK-G0704-ZS-Y
尺寸 SIZE	A4		