








P.C.B LAYOUT



MATING PLUG
Jack Insertion Depth: 9.15 mm

SCHEMATIC	
Model	DC-022K
Center Pin	Ø2.0 mm
	Ø2.5 mm

	MATERIAL	PLATING
center pin	Brass	tin
terminal 1	Brass	tin
terminal 2	Sus	tin
terminal 3	Brass	tin
plastic	Pbt	
cover	Pf	

							DSND		DATE		SCALE: N/A	MODEL TYPE: DC POWER JACK		
					ANGLAR	±5°	DWN		DATE		VIEW: 	PART NO.:		
△x					X.X	±0.2mm	CHKD		DATE		UNIT: mm	DWG NO.: DC-022K-2.5		
△x					X.XX	±0.1mm								
△x					X.XXX	±0.05mm								
MARK	DESCRIPTION		DATE	REVISED	APPROVED		APPD		DATE		SIZE: A4			
REVISIONS						UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO.,LIMITED				WEIGHT	SHEET	REVISION
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn						1.0g						1/1	A0	