



RECOMMENDED PLUG

SPECIFICATION
 1.Rating : DC 20V 5.5A;
 2.Contact resistance: $\leq 0.03\Omega$;
 3.Insulation resistance: $\geq 100M\Omega$ (DC250V);
 4.Withstand voltage: 500VAC ;
 5.Insertion and extraction force: 3-30N;
 6.life test: 5,000 cycles.

SCHEMATIC	
Model	DC-C033D-5.5A
Center Pin	$\varnothing 2.0$ mm $\varnothing 2.5$ mm

	MATERIAL	PLATING
center pin	Brass	tin
coat	Sus	
terminal 2	Phosphor Bronze	tin
terminal 3	Brass	tin
terminal 4	Brass	tin
terminal 5	Brass	tin
plastic	Pa9t	

					ANGLAR	$\pm 5^\circ$	DSND		DATE		SCALE: N/A	MODEL TYPE: DC POWER JACK	
Δ X					X.X	± 0.2 mm	DWN		DATE		VIEW:	PART NO.:	
Δ X					X.XX	± 0.1 mm	CHKD		DATE		UNIT: mm	DWG NO.:	
Δ X					X.XXX	± 0.05 mm	APPD		DATE		SIZE: A4	DC-C033D-5.5A-2.0	
MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES			XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
REVISIONS											1.0g	1/1	A0
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn													