





SPECIFICATION
Contact Rating: 50mA,12V DC
Contact Resistance: 100mΩ max
Insulation Resistance: 100mΩ min.500V DC
Dielectric Strength: 250V AC/1minute
Travel: 0.15mm
Operating Temp: -30℃~+85℃
Storage Temp: -30℃~+80℃

PAPT NO	TS-1010B-X-X
Operating Force	A: 100gf B: 160gf C: 260gf
Height	II: 3.5
Position Foot	A:With B:without

⑤	Terminal	—	2	Brass (0.30t)	Plating silvering	—
④	Contact	—	1	F.ag/Sus	Natural	—
③	Base	—	1	Lcp		—
②	Cover	—	1	Brass	Plating Nickel	—
①	Keystake	—	1	Pa46		—
ITEM	PAPT NAME	TER.NO	QTY	MATERIAL	FINISHING	REMARK

						DSND		DATE		SCALE: N/A	MODEL TYPE: TACT SWITCH			
					units: mm	DWN		DATE		VIEW: 	PART NO.:			
△ X					tolerance:	CHKD		DATE		UNIT: mm	DWG NO.:			
△ X					X.X ±0.2mm						TS-1010B-X-X			
△ X					X.XX ±0.1mm	APPD		DATE		SIZE: A4				
MARK	DESCRIPTION			DATE	REVISED	APPROVED								
REVISIONS						UNSPECIFIED TOLERANCES			XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn												1.0g	1/1	A0