


SPECIFICATION

- ▲ 1、Electrical rating : DC 12V 3.8A
- 2、Contact resistance : < 20mΩ(initial)
- 3、Insulation resistance : > 1000MΩ(500VDC between open contacts)
- 4、Dielectric strength : >1500V 1 minute
- 5、Electrical life : 6000 cycles
- 6、Temperature rise at the terminal : Max.30°C
- 7、Solder ability of terminal : Max350°C, 3S(no pressure may be placed in the terminals when soldering by hand)
- 8、Any Cd Pb Hg etc and it's compounds is not include in this product

PATENT NO. : M376887



SCHMATIC

德利威電子股份有限公司
DAILYWELL ELECTRONICS CO.,LTD.

符號	原尺寸	修改後尺寸	變更日期
1 (A)	加註PIN與孔徑尺寸公差		SEP-23-2014
2 (B)	加標端子外露高度3.80,修正開孔尺寸		SEP-12-2017
3 (C)			
4 (D)			
5 (E)			

SCALE(比例): 2:1
TOLERANCE (公差):
 0.00 mm ± 0.25mm
 0.0 mm ± 0.40mm
ANGULAR: ± 5°
FILE NAME : RJ0006

TITLE 圖名	DC POWER JACK WITH SWITCHES		SIZE 圖紙	A4
DWG NO. 圖號	RJ-005		UNIT 單位	inch mm
REV. 版本	C	DATE 日期	OCT - 12 - 2011	SHEET 張數
CHECKED BY 審核	陳燈財		DRAWN BY 製圖	IRENE