



剖视图

**Specifications:**  
 Contact Resistance: 30mΩ max. at DC 100mA  
 Insulator Resistance: 1000mΩ min. at DC 500V  
 Current Rating: 1AMP  
**Dielectric Withstanding**  
 Voltage: AC 500V For 1 minute  
 Operating Temperature: -55° C+105° C  
 Contact: Male Brass

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	深圳市如科盟实业有限公司 CHANKLEMENT INDUSTRY CO., LTD	TITLE:	
CHECKED:	DATE:		EDK-9/9 黑 通孔带螺母 #4-40UNC	
DRAWN:	DATE:	P/N	SCALE	REV.
LYP	2009-11-28	/	free	A
FILE NO.		CHANK-EDK-0001	REV.	NS000