



Specification
Current Rating : 1A
Contact Resistance : 20mΩ Max
Insulation Resistance : 1000MΩ Min.at 500V DC
Dielectric Withstanding Voltage : 500V AC for 1 Minute
Operation Temperature : -55 ° C~+105 ° C

Material
Insulator : P.B.T+30%Glass Fiber(UL94V-0)
Contact : Phosphor Bronze or Brass
Contact Plated : 0.8u" Gold over Nickel or Tin

POLES	PART No.	Dim. A	Dim. B	Dim. C
6	101-6P	12.19	5.08	6.35
8	101-8P	14.73	7.62	8.89
10	101-10P	17.27	10.16	11.43
12	101-12P	19.81	12.70	13.97
14	101-14P	22.35	15.24	16.51
16	101-16P	24.89	17.78	19.05
18	101-18P	27.43	20.32	21.59
20	101-20P	29.97	22.86	24.13
24	101-24P	35.05	27.94	29.21
26	101-26P	37.59	30.48	31.75

POLES	PART No.	Dim. A	Dim. B	Dim. C
30	101-30P	42.67	35.56	38.83
34	101-34P	47.75	40.64	41.91
40	101-40P	55.37	48.26	49.53
44	101-44P	60.45	53.34	54.61
50	101-50P	68.07	60.96	62.23
56	101-56P	75.69	68.58	69.85
60	101-60P	80.77	73.66	74.93
62	101-62P	83.31	76.20	77.47
64	101-64P	85.85	78.74	80.01

TOLERANCE TABLE

.0	±0.20
.00	±0.10
.000	±0.05

APPROVED: _____ DATE: _____

CHECKED: _____ DATE: _____

DRAWN: _____ DATE: _____

LYF _____ DATE: 2008-04-07

CLIENT P/N /
101-XP 三件式 有凸
深州市旭科盟实业有限公司
CHANKEMENG INDUSTRYCO., LTD

TITLE:
101-XP 三件式 有凸

UNIT	SCALE	REV.
mm	Free	A
FILE NO.	Clientw-101-0001	