



SPECIFICATIONS

- 1、Current Rating: 2A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
- 4、Contact Resistance: $20\text{m}\Omega$ Max
- 5、Insulation Resistance: $1000\text{M}\Omega$ Min
- 6、Withstanding Voltang: 1500V AC/minute
- 7、Material: Phosphoric bronze Tin-plated
- 8、Applicable Wire Sizes: AWG#22~28#

				TOLERANCE UNLESS OTHERWISE		DRAWN	CK tan	XFCN兴飞连接器有限公司 CONNECTORS XFCN CONNECTORS CO., LTD.		SHEET	1/1
				X.	± 0.30	X°	$\pm 5^{\circ}$			CHKD	DATE
				.X	± 0.20	.X°	$\pm 2^{\circ}$	APPD	PRODUCT NAME	2.54mm IDC Style Connectors	
				.XX	± 0.08	.XX°	$\pm 1^{\circ}$	VIEW	PART. NO.	T2050-PS	
				.XXX	± 0.03	.XXX°	$\pm 0.5^{\circ}$			SCALE	1:1
				VER	MODIFICATION	DRAW	DATE			DWG NO.	009