

环保物料

TEL:0769-82001899

A

B

C

D

E

F

G

A

B


C

D


E

F


G




Y型端子




一般型端子




6P 小鼻/无槽




8P 大鼻/无槽




6P 小鼻/单槽








8P 小鼻/单槽







6P 小鼻/单槽



8P 小鼻/单槽



10P-12P 单槽



14P-64P 双槽

NOTES:

Insulator Material: PBT, UL 94V-0

Contact Plating: Gold flash over nickel

Contact Material: Brass

Current Rating : 1A AC,DC

Contact Resistance: 20MΩ Max.

Dielectric Withstanding: AC 500V

Insulator Resistance: 1000MΩ Min.

Operating Temp.: -40°C~+105°C

NUMBER OF POSITIONS	DIMENSION		
	A	B	C
06	12.32	5.08	1.9
08	14.86	7.62	小1.9/大3.8
10	17.40	10.16	3.8
12	19.94	12.70	3.8
14	22.48	15.24	3.8
16	25.02	17.78	3.8
18	27.56	20.32	3.8
20	30.10	22.86	3.8
22	32.64	25.40	3.8
24	35.18	27.94	3.8
26	37.72	30.48	3.8
30	42.80	35.56	3.8
34	47.88	40.64	3.8
36	50.42	43.18	3.8
40	55.50	48.26	3.8
44	60.58	53.34	3.8
50	68.20	60.96	3.8
60	80.90	73.66	3.8
64	85.98	78.74	3.8

TOLERANCE UNLESS OTHERWISE

X.	±0.30	X°	±5°
.X	±0.20	.X°	±2°
.XX	±0.08	.XX°	±1°
.XXX	±0.03	.XXX°	±0.5°

DRAWN

CK tan

CHKD

APPD

VIEW



**XFCN兴飞连接器有限公司**  
CONNECTORS XFCN CONNECTORS CO., LTD.

PRODUCT NAME **2.54mm IDC Socket Connectors**

PART. NO. **I254-2xXX-G-3-B**

SHEET 1/1

DATE 2010. 4. 12

UNITS mm

SCALE 1:1

DWG NO. 009

AO

VER

MODIFICATION

DRAW

DATE

1

2

3

4

5

6

7

8

9

10