








PART NO.	
K5-1632SA-01	K5-1632SN-01

NOTE:
Rating: DC 12V 50mA
Operating Force: 20±10gf
Lifetime: 100,000 Cycles

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑤	Contact Spring	—	1	Be Alloy	Ag Plated	—
④	Terminal	—	4	Phosphor Bronze	Ag Plated	—
③	Base	—	1	PA46	Black	—
②	Housing	—	1	PA46	Black	—
①	Slider	—	1	PA46	Black	—

APPROVALS		DATE	ELECTRONICS CO.,LTD	
DRAWN	J.X.Zhang	2014/5/28	DETECTOR SWITCHES	

APPROVALS		TITLE:		PART NO.	
CHECKED					
APPROVALS					
TOLERANCES ARE		30~0.15	±0.30	ANGLE	UNIT: mm
		10~30	±0.20		SCALE: 1:1
		5~10	±0.15		PROJ.
		~ 5	±0.10		SHEET 1 OF 1
ECN NO.	REV.	DATE.	DESCRIPTION.		
	A		NEW		
CHANGE.		CHECK.	APPRO.		