




Circuit Diagram

NOTE:
Rating: DC 30V 0.1A
Operating Force: $30 \pm 10\text{gf}$
Lifetime: 100,000 Cycles
PCB Layout(Pattern side)



PART NO.	
K5-1215DA-01	K5-1215DN-01

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑤	Contact Spring	—	1	Be Alloy	Ag Plated	—
④	Terminal	—	4	Phosphor Bronze	Ag Plated	—
③	Base	—	1	LCP	Black	—
②	Cover	—	1	SUS	Natural	—
①	Slider	—	1	PA46	Black	—

APPROVALS		DATE	ELECTRONICS CO.,LTD	
DRAWN	J.X.Zhang	2016/7/21		

						CHECKED				TITLE:		DETECTOR SWITCHS							
						APPROVALS				PART NO.		K5-1215D□-□□							
						TOLERANCES ARE		30~12.1 10~30 5~10 ~ 5		ANGLE		UNIT: mm		SCALE: 1:1		PROJ. 		SHEET 1 OF 1	