







组装示意图

建议开槽尺寸
单边放大0.2mm

Contact Number	Signal Name	Remarks
1#	VBUS	Power
2#	D-	Date-
3#	D+	Date+
4#	ID	Reserve or Gound
5#	GND	Gound

SPECIFICATIONS:

1. ELECTRICAL CHARACTERISTICS:
 - 1.1. RATING: 3A(PIN1&5), 0.5A(PIN2&3&4);
 - 1.2. CONTACT RESISTANCE: 30 mΩ MAX.(INITIAL);
 - 1.3. DIELECTRIC WITHSTANDING: 500V AC MIN.;
 - 1.4. INSULATION RESISTANCE: 1000MΩ MIN.;
 2. DURABILITY: 10,000 CYCLES MIN.;
 3. INSERTION FORCE: 3.5Kgf (35N) Max.;
 4. EXTRACTION FORCE: 0.8Kgf (8N) Min.;
 5. WATER PROOFNESS: THIS PRODUCT IS BASED ON IPX7(1m,30min)
 6. PLUG INTERFACE DIMENSIONS CONFORM TO USB2.0 SPEC.
7. PACKAGING: TAPE & REEL.

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑦	Oval ring	—	1	Rubber	Black	—
⑥	Glue	—	1	—	Black	—
⑤	U-shaped frame	—	1	Copper alloy	Ni Plated	—
④	Inner shell	—	1	Copper alloy	Ni Plated	—
③	Terminal	—	5	Copper alloy	Au Plated	—
②	Outer shell	—	1	Nylon	Black	—
①	Body	—	1	Nylon	Black	—

[illegible]