








规格说明: Specifications:

电气特性: Electrical:

1. 额定电流: Current Rating
2. 额定电压: Voltage Rating
3. 1A/contact terminal
3. 接触电阻: Contact Resistance
30 milliohms MAX
4. 耐电压: Dielectric Withstanding Voltage:
500 V AC AT Sea Level
5. 绝缘阻抗: Insulation Resistance:

物理性能: Mechanical:

- 1.插拔力: Connector Mate and Umate Force
Mate force:3.57kgf(MAX)
Umate force:1.02kgf(MIN)
- 2.端子保持力: Terminal Retention
1.0kgf(MIN)

RECOMMENDED P.C.B. LAYOUT

[illegible]