



Recommended PCB Layout

规格说明: Specifications:
电气特性: Electrical:

1. 额定电流: Current Rating
1.5A/contact terminal
2. 额定电压: Voltage Rating
30V DC
3. 接触阻抗: Contact Resistance
30 milliohms MAX
4. 耐电压: Dielectric Withstanding Voltage:
500 V AC AT Sea Level
5. 绝缘阻抗: Insulation Resistance:
1000MEGA ohms MIN

| PART NO | H |
|---------------|------|
| U-A-24DD-Y-11 | 6.30 |
| U-A-24DD-Y-12 | 6.80 |

| ③ | Base | 1 | NYLON | | | |
|----------------|--------------|----------|------------------------|------------|--------------|--------|
| ② | Terminal | 4 | Phosphor Bronze | Ag Plated | | |
| ① | Housing | 1 | SPCC | Sn Plated | | |
| ITEM | PART NAME | TER'NO. | QTY. | MATERIAL | FINISHING | REMARK |
| APPROVALS | | DATE | | | | |
| DRAWN | xu qi feng | 2018/8/1 | HROELECTRONICS CO.,LTD | | | |
| CHECKED | | | USB CONNECTOR | | | |
| APPROVALS | | | TITLE: PART NO. | | | |
| TOLERANCES ARE | 30~80L ±0.30 | ANGLE | UNIT: mm | SCALE: 1:1 | PROJ: | |
| | 10~30 ±0.25 | | DRAWING NO. | | SHEET 1 OF 1 | |
| | 5~10 ±0.20 | ±2' | | | | |
| | ~5 ±0.15 | | | | | |
| ECN NO. | REV. | DATE. | DESCRIPTION. | CHANGE. | CHECK. | APPRO. |
| | A | | NEW | | | |