







环保物料

TEL: 0769-82001899



SPECIFICATIONS

Voltage rating: 250V AC, DC
 Current rating: 3A, AC, DC
 Withstanding Voltage: 1000V AC/minute
 Insulation resistance: 1000M min
 Temperature range: -25 °C ~ +85 °C
 Contact resistance: 10m max
 Housing Material: LCP UL94V-0
 Pin Material: Brass
 Contact Area Plating: Tin-Plated



Type	Dimension mm					Type	Dimension mm				
	A	B	C	D	E		A	B	C	D	E
2	2.50	10.00	5.95			9	20.00	27.50	23.45	18.30	17.00
3	5.00	12.50	8.45	3.30	2.50	10	22.50	30.00	25.95	20.80	19.50
4	7.50	15.00	10.95	5.80	4.50	11	25.00	32.50	28.45	23.30	22.00
5	10.00	17.50	13.45	8.30	7.00	12	27.50	35.00	30.95	25.80	24.50
6	12.50	20.00	15.95	10.80	9.50	13	30.00	37.50	33.45	28.30	27.00
7	15.00	22.50	18.45	13.30	12.00	14	32.50	40.00	35.95	30.80	29.50
8	17.50	25.00	20.95	15.80	14.50	15	35.00	42.50	38.45	33.30	32.00

3	③	底座	LCP	1	UL94-V0
2	②	焊片	黄铜	2	镀锡
1	①	接触件	黄铜	N*	镀锡
序号	图号	名称	材料	数量	附件

TOLERANCE UNLESS OTHERWISE

X.	±0.30	X°	±5°
.X	±0.20	.X°	±2°
.XX	±0.08	.XX°	±1°
.XXX	±0.03	.XXX°	±0.5°

DRAWN	CK tan
CHKD	
APPD	
VIEW	

XFCN兴飞连接器有限公司
 CONNECTORS XFCN CONNECTORS CO., LTD.

PRODUCT NAME	2.50mm Crimp Style Connectors
PART. NO.	M2501RSF-XX-LP

SHEET	1/1
DATE	2010. 4. 12
UNITS	mm
SCALE	1:1
DWG. NO.	009

AO
VER

MODIFICATION

DRAW

DATE