



300V 10A 22-14AWG 2.5mm²
 Poles: 2P&3P-24P
 Pitch: 5.0mm (.197")

Materials

Housing: PBT(UL 94-0)
 Wire Protector: Stainless Steel
 Solder Pin: Brass, Tin Plated
 Screw: M3, Steel (A3), Zinc Plated
 Torque: 0.5N.m

设计/Drawn by	绘图/Drawn by	审核/Checked by	批准/Approved by	备注/Remarks
-------------	-------------	---------------	----------------	------------

		新莱亚电子 XINLAIYA ELECTRONIC CO., LTD	
图名/Title	文件编号/Title No.	图号/Title No.	图例/Title No.
	XY300VA-5.0		

单位/Unit	mm
---------	----

序号/No.	更改记录/Revision note	签名/Signature	日期/Date
--------	--------------------	--------------	---------