



300V 15A 22-14AWG 1.5mm²

Poles: 2P&3P-24P

Pitch: 5.0mm (.197")/5.08mm (.200")

Materials

Housing: PBT (UL 94V-0)

Wire Protector: Stainless Steel

Solder Pin: Brass, Tin Plated

Screw: M2.5, Steel (A3), Zinc Plated

Torque: 0.4N.m

设计/Designed by: 绘图/Drawn by: 审核/Checked by: 批准/Approved by: 公差/General Tolerances

图名/Title	文件编号/File No.	X. ±0.2	X. ° ±2°
XY301V-A		.X ±0.1	.X ° ±1°
-B	页序/Sheet	.XX ±0.05	.XX ° ±0.5°
		.XXX ±0.01	

单位/Units: MM