


300V 20A 26-12AWG 2.5mm²
 Poles: 2P&3P-24P
 Pitch: 5.0mm (.197")

Materials

Housing: PA66 (UL 94V-0)
 Solder Pin: Brass, Tin Plated
 Wire Cage: Brass, Nickel Plated
 Screw: M3.0, Steel (A3), Zinc Plated
 Torque: 0.5N.m

1	3.4更改为3.2	王维东	2010.5.21
序号/RevNo.	更改记录/Revision note	签名/Signature	日期/Date

设计/Designed by	绘图/Drawing by	审核/Checked by	批准/Approved by	未注公差 General Tolerance
				X: ±0.2 X': ±2" .X: ±0.1 .X': ±1" .XX: ±0.05 .XX': ±0.5" .XXX: ±0.01
 新莱亚电子 XINLAIYA ELECTRONIC CO., LTD		图名/Title	文件编号/FILE NO.	X: ±0.2 X': ±2" .X: ±0.1 .X': ±1" .XX: ±0.05 .XX': ±0.5" .XXX: ±0.01
备注/Remark		XY129RA-5.0	页序/Sheet	单位/Units: mm