




序号/revno. 更改记录/revision note

签名/signature

日期/date



150V 6A 26-18AWG 1.0mm²

Poles: 2P&3P-24P

Pitch: 2.54mm (.100")

Materials

Housing: PA66 (UL 94V-0)

Solder Pin: Brass, Tin Plated

Wire Cage: Brass, Nickel Plated

Screw: M1.6, Steel (A3), Zinc Plated

Torque: 0.1N.m

设计/Designed by

绘图/Drawing by

审核/Checked by

批准/Approved by

公差/General Tolerance

图名/Title

文件编号/File No.

X.° ±2°

XY308-2.54

页序/Sheet

.X ±0.1°

备注/Remark

.XX ±0.05°

.XXX ±0.01°

单位/units: mm

序号/revno. 更改记录/revision note

签名/signature

日期/date



XINLAIYA ELECTRONIC CO., LTD

新莱亚电子