


(250) 端子 TERMINAL

### 技术参数 SPECIFICATIONS

- 线数 (Poles) : 1、2、3
- 适用线规 (Applicable wires) : AWG24#~16#
- 温度范围 (Temperature range) : -25℃~85℃
- 额定电压 (Voltage rating) : 300V.Ac/Dc
- 额定电流 (Current rating) : 15A max
- 接触电阻 (Contact resistance) :  $\leq 0.01\Omega$
- 绝缘电阻 (Insulation resistance) :  $\geq 1000M\Omega$
- 耐压 (Withstand voltage) : 2000V.Ac/1min
- 材料 (Material) :
  - 插头 (Plug housing) : 尼龙 (PA66) UL94V-2(0)
  - 插座 (Receptacle housing) : 尼龙 (PA66) UL94V-2(0)
  - 端子 (Terminal) : 黄铜 (Brass Tin/plated)


型号 Type			适用线规 Applicable wires		材料 Material	尺寸 Dimensions (mm)			材料厚度 Thickness	示例 Sample	数量 Quantity
			mm <sup>2</sup>	AWG#		W	L	E			
HX6.0K-01PT	HX6.3N-01T	730267-1	0.22~0.5	24~20	黄铜 Brass	7.6	19.5	7.4	0.4	A	5000PCS/卷 4000PCS/卷
HX6.0K-21PT	HX6.3N-21T	730268-1	0.5~1.25	20~16		7.6	19.5	7.4	0.4		
HX6.0K-41PT	HX6.3N-41T	—	2.0~3.0	14~12		7.6	19.5	7.4	0.4		
HX6.0K-01RT	HX6.3P-01T	740253-1	0.22~0.5	24~20	黄铜 Brass	6.0	24.7	10.3	0.4	B	5000PCS/卷 4000PCS/卷
HX6.0K-21RT	HX6.3P-21T	740254-1	0.5~1.25	20~16		6.0	24.7	10.3	0.4		
HX6.0K-41RT	HX6.3P-41T	—	2.0~3.0	14~12		6.0	24.7	10.3	0.4		

HX6.0K-PT (HX6.3N-+T)



(A)

HX6.0K-RT (HX6.3P-+T)



(B)

线数 (Poles)	额定电压 (Voltage Rating)	额定电流 (Current Rating)	插头 (Plug housing)	插座 (Receptacle housing)
1	300V	15A	<p>HX6.0K-1PF (610041/35955-0120)</p>	<p>HX6.0K-1R (620040/35955-0110)</p>
2	300V	13A	<p>HX6.0K-2PF (610043/35955-0220)</p>	<p>HX6.0K-2R (620042/35955-0210)</p>
3	300V	12A	<p>HX6.0K-3PF (610045/35955-0320)</p>	<p>HX6.0K-3R (620044/35955-0310)</p>