



LED colour(LED颜色)	Part No.(料号)
White(白色)	K6-6165D01
Red(红色)	K6-6165D02
Blue(蓝色)	K6-6165D03
Green(绿色)	K6-6165D04



PCB layout pattern Side



Circuit Diagram

Typical Specifications

1. Rating : DC 12V 50mA
2. Operating Force : 160 ± 50 gf
3. Contact Resistance : 100mΩMAX
4. Life : 100,000 Cycles Min

② Terminal	Phosphor bronze	Ag Plating
① Housing	Nylon	Black
ITEM PART NAME	TERN.O.	QTY.
APPROVALS	DATE	
DRAWN	JIANKUN.LU/2015/05/25	
CHECKED	TITLE: LED Tact Switch	
APPROVALS	PART NO.	K6-6165D
TOLERANCES ARE	30~12L ±	±0.30
	10~30	±0.20
	5~10	±0.15
	~5	±0.10
	ANGLE	±2°
	UNIT:	mm
	SCALE:	1:1
	DRAWING NO.	
	PROJ:	
	SHEET	1 OF 1



ELECTRONICS CO.,LTD

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			