



4PIN以上





2PIN和3PIN



Recommend PCB Layout

Specifications(规格) :

- Voltage rating(额定电压): 250V AC / DC
- Current rating(额定电流): 3A AC / DC
- Withstanding voltage(耐压值): 1500V AC/minute
- Temperature range(工作温度): -25°C~+85°C
- Insulation resistance(绝缘电阻): ≥500MΩ
- Contact resistance(接触电阻): ≤10mΩ
- After environmental testing(环境测试后): ≤20mΩ



Poles	Dimensions (mm)		
	A	B	C
2	7.50	5.80	2.50
3	10.00	8.30	5.00
4	12.50	10.80	7.50
5	15.00	13.30	10.00
6	17.50	15.80	12.50
7	20.00	18.30	15.00
8	22.50	20.80	17.50
9	25.00	23.30	20.00
10	27.50	25.80	22.50
11	30.00	28.30	25.00
12	32.50	30.80	27.50
13	35.00	33.30	30.00
14	37.50	35.80	32.50
15	40.00	38.30	35.00

X2508 W V X-XX X-N0 SN XX

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- ①系列
②类别: W-WAFER类
③外观形态:
V-180°
④成型方式:
空码-DIP
⑤PIN数:
单排-XX
⑥空PIN位置及特殊码
⑦材质:
N0-PA66 94V-0 N2-PA66 94V-2
⑧电镀类别:G**-镀金 V**-镀全金
*01-1U" *02-2U" *03-3U" *05-5U"
*10-10U" *15-15U" *30-30U" *50-50U"
SN-镀亮锡(70-120U") SN1-镀亮锡(120U"Min.)
SW-镀雾锡 HS-高温锡
⑨颜色:
空码-本色或普通色

X2508WV-XX-N0SN	Nylon 66 UL 94V-0	Brass	Tin-Plated	X2508H
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Terminal

For and on behalf of
XKB INDUSTRIAL PRECISION CO., LIMITED
香港星坤工業精密有限公司

	XKB INDUSTRIAL PRECISION CO., LIMITED 香港星坤工業精密有限公司					ANGULAR	± 5°
△ X						L ≤ 4	± 0.2
△ X						4 < L ≤ 16	± 0.3
△ X						16 < L ≤ 63	± 0.4
MARK	DESCRIPTION		DATE	REVISED	APPROVED	L > 63	± 0.5
REVISIONS							UNSPECIFIED TOLERANCE:
Authorized Signature(s)							

DSND		DATE		SCALE: N/A	MODEL TYPE: X2508WV-XX-N0SN
DWN		DATE		VIEW:	PART NO.: 2.50 mm Crimp Style connectors
CHKD		DATE		UNIT: mm	DWG NO.:
APPD		DATE		SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED					WEIGHT 1.0g
					SHEET 1/1
					REVISION A0