





RoHS





短柄 Short handle



PCB Layout(Pattern Side)



Circuit Diagram



凸柄 Convex handle

NOTE:

- 1.Rating: 24V 25mA DC
- 2.Insulation Resistance: $\geq 100 \text{ M}\Omega$
- 3.Withstand voltage:AC 500V 1Minute
- 4.Operating Force Range: 500gf Max
- 5.Mechanical Life:3,000 Cycles

| | | | | | |
|-----|----------|--------|-----|------------------|--------------|
| Ⓔ | Terminal | | 12 | Brass | Gold plating |
| Ⓓ | Shrapnel | | 6 | Beryllium copper | Gold plating |
| Ⓒ | Handle | | 6 | PA46 | White |
| Ⓑ | Cover | | 1 | PPS | Black |
| Ⓐ | Base | | 1 | PPS | Black |
| NO. | Name | Number | Qty | Materil | Remarks |

| | | | | | | | | | | | |
|----------------------------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|
| Number of digits(位数) | 1P | 2P | 3P | 4P | 5P | 6P | 7P | 8P | 9P | 10P | 12P |
| Cover/black 凸柄 盖子/黑色 短柄 | TL-01 TL-01D | TL-02 TL-02D | TL-03 TL-03D | TL-04 TL-04D | TL-05 TL-05D | TL-06 TL-06D | TL-07 TL-07D | TL-08 TL-08D | TL-09 TL-09D | TL-10 TL-10D | TL-12 TL-12D |

YUANDI® Yuandi Electronics Co, Ltd
元迪

| | | | |
|----------|------|-------|------------|
| design | date | name | DIP SWITCH |
| Review | date | model | TL-06 |
| Approved | date | | |

| | | | | | | |
|-----------------|------------|-----|------|----|-------------|----|
| Drawing number: | Proportion | 1:1 | unit | mm | gape number | A4 |
|-----------------|------------|-----|------|----|-------------|----|

modify Review Approved Tolerance not specified

| | |
|-------|-------|
| angle | ±2' |
| 10~30 | ±0.30 |
| 5~10 | ±0.20 |
| ~ 5 | ±0.10 |