



Schematic



P.C.B LAYOUT(copper-sided view)

Rating:0.5A 30V DC
 Contact Resistance:100 mΩ Max.
 Operating temperature:-20℃~70℃
 Operating force:3-20N
 Operating Life:5,000cycles

②	Terminal	4	Phosphor bronze	Au Plating	
①	Housing	1	Nylon	Black	
ITEM	PART NAME	TERN.O.	QTY.	MATERIAL	FINISHING
APPROVALS		DATE			

DRAWN	J.X.Zhang	DATE	2013/11/11	TITLE: PHONE JACKES	
CHECKED				PART NO. PJ-327D	
APPROVALS				SCALE: 1:1	PROJ. SHEET 1 OF 1

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			
TOLERANCES ARE						
		30 ^{±0.15}	±0.30	ANGLE		
		10 ^{±0.10}	±0.20	UNIT: mm		
		5 ^{±0.10}	±0.15	±Z'	DRAWING NO.	