



DIM. Poles	DIM A	DIM B	DIM C
2	4.25	1.25	7.55
3	5.50	2.50	8.80
4	6.75	3.75	10.05
5	8.00	5.00	11.30
6	9.25	6.25	12.55
7	10.50	7.50	13.80

DIM. Poles	DIM A	DIM B	DIM C
8	11.75	8.75	15.05
9	13.00	10.00	16.30
10	14.25	11.25	17.55
11	15.50	12.50	18.80
12	16.75	13.75	20.05
13	18.00	15.00	21.30

DIM. Poles	DIM A	DIM B	DIM C
14	19.25	16.25	22.55
15	20.50	17.50	23.80
16	21.75	18.75	25.05
17	23.00	20.00	26.30
18	24.25	21.25	27.55

- 技术参数 SPECIFICATIONS
- ◆ 适用线规：AWG#28~#32
- ◆ Applicable Wire: AWG#28~#32
- ◆ 额定电压：125V DC,AC(rms)
- ◆ Rated voltage: 125V DC,AC(rms)
- ◆ 额定电流：1A
- ◆ Rated Current: 1A
- ◆ 耐压值：500V AC/minute
- ◆ Withstand voltage: 500V AC/min.
- ◆ 工作温度：-25°C ~ +85°C
- ◆ Working Temp：-25°C ~ +85°C
- ◆ 绝缘电阻：≥1000 MΩ
- ◆ Insulation resistance: ≥1000 MΩ
- ◆ 接触电阻：≤20mΩ
- ◆ Contact resistance: ≤20mΩ

P.C.B Layout

ITEM	PART NAME	TER.NO.	QTY.	MATERIAL	FINISHING	REMARK
③	Solder Tab	—	2	Phosphor bronze	Ag-PLATED	—
②	PIN	—	—	Phosphor bronze	Ag-PLATED	—
①	Base	—	1	PA46	—	—

APPROVALS	DATE
DRAWN	2015.03.17

CHECKED		TITLE:	
APPROVALS		Bar Connector Series	
TOLERANCES ARE		SCALE: 1:1	PROJ:
30~0.1±	±0.30	UNIT: mm	SHEET 1 OF 1
10~0.30	±0.20		
5~1.0	±0.15		
~5	±0.10		

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			



ELECTRONICS CO., LTD