






由 Autodesk 教育版产品制作



截面 1-1



- SPECIFICATIONS:
- ELECTRICAL CHARACTERISTICS:
 - CONTACT RESISTANCE: $30\text{m}\Omega$ MAX.
 - DIELECTRIC WITHSTANDING VOLTAGE: 100V AC FOR ONE MINUTE.
 - INSULATION RESISTANCE: $100\text{M}\Omega$ MIN. MEASURED BY 500 VDC
 - MECHANICAL CHARACTERISTICS:
 - INSERTION FORCE: $0.5\sim 2.0\text{kgf}$ (REF.)
 - WITHDRAWAL FORCE: $0.8\sim 2.0\text{kgf}$ (REF.)
 - LIFE TEST: 10,000 CYCLES.
 - TO CONFORM TO THE KRCONN HAZARDOUS SUBSTANCE FREE SPEC.



RECOMMENDED P.C.B. LAYOUT (T:1.00mm)
TOLERANCE UNSPECIFIED $\pm 0.05\text{mm}$

A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1		
A6	DP1	B7	DN2
A7	DN1	B6	DP2
		B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

6	SHELL	STAINLESS STEEL	Ni Plated	1PCS
5	SHIELDING PLATE	STAINLESS STEEL	---	1PCS
4	MD	HIGH TEMPERATURE PLASTIC	BLACK	1PCS
3	CONTACT	COPPER ALLOY	Au/Ni Plated	1SET
2	CONTACT	COPPER ALLOY	Au/Ni Plated	1SET
1	HOUSING	HIGH TEMPERATURE PLASTIC	BLACK	1PCS
NO.	DESCRIPTION	MATERIAL	REMARKS	QTY

产品图

PRODUCT CHART DWG

公差一览表

TOLERANCE UNLESS OTHERWISE			
X.	± 0.30	X.	$\pm 5^\circ$
.X	± 0.25	.X	$\pm 2^\circ$
.XX	± 0.15	.XX	$\pm 1^\circ$
.XXX	± 0.10	.XXX	$\pm 0.5^\circ$

深圳市精拓金电子有限公司

单位	MM	制图	YANG	制图料号	
UNITS	MM	DRAWING	YANG	PRODUCT PART NO.	
比例	1:1	审核	郭志富	产品名称	TYPE C 14P母座180度SMT H=10.0
SCALE	1:1	CHKD	郭志富	PRODUCT NO.	
日期	2019.11.23	核准	黄国荣	角法	
DATE	2019.11.23	APPD	黄国荣	VIEW	
				版本	AD
				VER	

由 Autodesk 教育版产品制作