




RoHS

MAPX

MODIFICATION

DRW

DATE



备注:


电气特性:Electrical:

1. 额定电流: 5A MIN ROR VBUS
0.25A MIN FOR OTHER
2. 接触阻抗: 40 milliohms MAX
3. 绝缘阻抗: 100MEGA ohms MIN
4. 耐压测试: 250V AC
5. 插拔力: Mate force: 10.0N (MAX)
Unmate force: 9.0N (MIN)
6. 使用寿命: 10000次
7. 工作温度: -55 ° C ~ 85 ° C

原材料:Material:

1. 塑胶: LCP+30%G.F UL94V-0
2. 端子: 7025高导铜
3. 外壳: 不锈钢SUS304 T=0.30mm

A1	GND	B12	GND
A2		B11	
A3		B10	
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC5
A9	VBUS	B4	VBUS
A10		B3	
A11		B2	
A12	GND	B1	GND



SPECIFICATION

胶芯LCP黑色; 端子高导铜镀金GF; 外壳不锈钢镀镍。

胶芯橙色; 端子高导铜镀金GF; 外壳不锈钢镀镍。

产品图

PRODUCT CHART DWG

公差一览表 TOLERANCE UNLESS OTHERWISE			
X.	±0.25	X.	±5.°
.X	±0.20	.X	±2.°
.XX	±0.15	.XX	±1.°
.XXX	±0.10	.XXX	±0.5°

深圳市精拓金电子有限公司
Shenzhen Jing Tuo Jin Electronics Co., Ltd.

单位 UNITS	MM	制图 DRAWING	XRQ	制图料号 PRODUCT PART NO.	
比例 SCALE	1:1	审核 CHKD	郭志富	产品名称 PRODUCT NO.	USB C TYPE 贴板母座16Pin SMT 四角插板
日期 DATE	2016-09-09	核准 APPD	黄国荣	角法 VIEW	版本 VER
					A0