


REVISIONS					
REV	NUMBER	DESCRIPTION	DWN	CHK	DATE
A		DESIGN			




- NOTES:
- ELECTRICAL:
 - VOLTAGE RATING:DCV 300V 10MS
 - CONDUCTANCE RESISTANCE:3.0 OHMMAX.
 - INSULATION RESISTANCE:5.0M OHM/MIN.
 - THE CABLE SHOULD BE 100% ELECTRICAL TEST
 - IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES.
 - MATERIAL:
 - SEE TABLE
 - ALL COMPONENTS ARE ROHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
④	套管	黑色热缩套管, OD:2.0MM	AS
③	端子	高仿IPEX 0.81 4代端子, 镀金	1
②	接头	SMA母头母针, 分体, 11牙, 镀金	1
①	同轴线	RF 0.81线材,颜色: 黑色, OD:0.81mm	AS

金航标电子有限公司

ALL DIMENSION ARE IN MM		DRAWN	DATE	I-PEX 0.81 4代 TO SMA /F L=100mm	
		Janny	2020-06-18		
COMPUTER GENERATED IN SOLIDWORKS		ENG.			
DO NOT SCALE THIS DRAWING		MFG.			
PROJECTION		Q.A.		GENERAL TOLERANCE FOR ANGLES X.X X.XX X.XXX	
				± 1° ± 0.3 ± 0.25 ± 0.150	
SIZE		Number	REV		
B			A		
SCALE: Free		TYPE	SHEET	1 OF 1	



技术详询

CUSTOMER P.N.:

4

3

2

1

4

3

2

1

A

B

C

D

A

B

C

D