

## D-Sub, MA AWG 20-24 crimp cont



Image is for illustration purposes only. Please refer to product description.

Part number	09 67 000 8576
Specification	D-Sub, MA AWG 20-24 crimp cont
HARTING eCatalogue	<a href="https://b2b.harting.com/09670008576">https://b2b.harting.com/09670008576</a>

### Identification

Category	Contacts
Series	D-Sub
Identification	Standard
Type of contact	Crimp contact

### Version

Gender	Male
Manufacturing process	Turned contacts
Performance level	1

### Technical characteristics

Conductor cross-section	0.25 ... 0.52 mm <sup>2</sup>
Conductor cross-section	AWG 24 ... AWG 20
Contact resistance	≤10 mΩ
Stripping length	4 mm

### Material properties

Material (contacts)	Copper alloy
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No



Pushing Performance

## Material properties

REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

## Commercial data

Packaging size	100
Net weight	0.1 g
Country of origin	Switzerland
European customs tariff number	85366990
eCl@ss	27440204 Contact for industrial connectors