


Pin	Part No	Current
φ 1.3	DC-022B-A130	5.0A
φ 2.0	DC-022B-A200	5.0A
φ 2.5	DC-022B-A250	8.0A

SPECIFICATION

- Rating : DC 30V 3A;
- Contact resistance : $\leq 0.03\Omega$;
- Insulation resistance : $\geq 100M\Omega$ (DC250V);
- Withstand voltage : 500VAC;
- Insertion and extraction force : 3-20N;
- life test : 5,000 cycles。



NO.	DESCRIPTION	QTY	MATERIAL	PLATING
4	PIN	1	H59 BRASS	Ni-Plating
3	SPRING	1	BRONZE C5210	Ag-Plating
2	FLAT PIECE	1	H62 BRASS	Ag-Plating
1	HOUSING	1	PA9T	

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: DC电源插座系列	
DECIMALS:	ANGLES:	PAR	DC-022B-AXXX
X:±0.5	X:±2°	DWN	KING
X.X:±0.3		CHKD	2013.07.08
X.XX:±0.2		APVD	
CUSTOMER COPY		SCALE 1:1	UNIT: mm
		SIZE:A4	SHEET:1F1
			REV:A

