




PIN	SIGNAL NAME	PIN	SIGNAL NAME
A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND



- NOTES:
- MECHANICAL:  
MATING FORCE: 5-20N.  
UNMATING FORCE: 8-20N.
  - ELECTRICAL:  
CURRENT: 5.0A MAX  
VOLTAGE: 20V MAX  
WITHSTANDING VOLTAGE: 300V AC  
CONTACT RESISTANCE: 40mΩ MAX INITIAL;  
50 mΩ MAX AFTER 10000 CYCLES
  - ENVIRONMENTAL:  
OPERATING TEMPERATURE RANGE -30°C ~ +80°C
  - Salt Spray: 24H



MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd			
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: USB C TYPE 母座 双排16P 立式SMT 四脚插板		
DECIMALS:	ANGLES:		PAR	TYPEC-303-ACP16	
X:±0.5	X:±2°		DWN	KING	2014.10.21
X.X:±0.3	X.X:±1°		CHKD	APVD	
X.XX:±0.2		SCALE 1:1	UNIT: mm		
CUSTOMER COPY		SIZE:A4	SHEET:1F1	REV:A	