

# HSF

NOTES:  
 Rated Current: 3.0A  
 Contact Resistance: 20mΩ max  
 Withstand Voltage: 1000V AC/Minute  
 Insulation Resistance: 1000MΩ min  
 Operation Temperature: -25°C to +85°C  
 Insulator Material: PBT + 30%G.F UL94V-0  
 Used with: WF2547-T  
 Mated with: WF2547-Wafer


## Ordering Information

WF2547 - 2 H XX X 0 1

No. of pins  
02P-20P

Color  
E=Beige  
W=White  
B=Black  
U=Blue

Packing  
0=PE Bag



Dimensional & Ordering Information:

Circuit	Part No.	Dimension	
		A	B
2x02	WF2547-2H02X01	2.54	5.08
2x03	WF2547-2H03X01	5.08	7.62
2x04	WF2547-2H04X01	7.62	10.16
2x05	WF2547-2H05X01	10.16	12.70
2x06	WF2547-2H06X01	12.70	15.24
2x07	WF2547-2H07X01	15.24	17.78
2x08	WF2547-2H08X01	17.78	20.32
2x09	WF2547-2H09X01	20.32	22.86
2x10	WF2547-2H10X01	22.86	25.40
2x12	WF2547-2H12X01	27.94	30.48
2x15	WF2547-2H15X01	35.56	38.10
2x18	WF2547-2H18X01	43.18	45.72
2x20	WF2547-2H20X01	48.26	50.80

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION	DRAW	DATE	SCALE	FIT	PART NO.
A1	2013/11/14	Add 2X02P Information		X.X	JHuang	2013/11/14	mm	A4	SEE TAB
AO	2012/09/28	NEW		X.XXX	CHECK		SIZE	1/1	TITLE: 2.54 Housing Dual Row "T" Type
				Angle	APPROVE		SHEET		Customer NO.
				DIM			PROJ.		

# WCON

Http: [www.wcon.com](http://www.wcon.com)

WCON-Dongguan  
 Tel: +86 769 85358920  
 Fax: +86 769 85358915  
 E-mail: [sales@wcon.com](mailto:sales@wcon.com)

WCON-Kunshan  
 Tel: +86 512 57468408  
 Fax: +86 512 57468468  
 E-mail: [sales@wcon.com](mailto:sales@wcon.com)