



**SPECIFICATIONS**

1. Voltage rating: 250V AC, DC
  2. Current rating: 3A, AC, DC
  3. Withstanding Voltage: 1000V AC/minute
  4. Insulation resistance: 800M min
  5. Temperature range: -25 ° C +85 ° C
  6. Contact resistance: 20m max
- WAFER

Housing Material: Nylon UL94V-0  
 Pin Material: Phosphor Bronze or Brass  
 Contact Area Plating: Plated Tin or Plated Gold  
 Mates with :P2029 series Housing  
 Poles:02-16P  
 Part No.: M2029R-xx-N0

Pin位数

P/N	DIM A	DIM B	DIM C
2	2.0	6.0	4.8
3	4.0	8.0	6.8
4	6.0	10.0	8.8
5	8.0	12.0	10.8
6	10.0	14.0	12.8
7	12.0	16.0	14.8
8	14.0	18.0	16.8
9	16.0	20.0	18.8
10	18.0	22.0	20.8
11	20.0	24.0	22.8
12	22.0	26.0	24.8
13	24.0	28.0	26.8
14	26.0	30.0	28.8
15	28.0	32.0	30.8
16	30.0	34.0	32.8

				TOLERANCE UNLESS OTHERWISE		DRAWN	CK tan	<b>XFCN兴飞连接器有限公司</b> CONNECTORS XFCN CONNECTORS CO., LTD.		SHEET	1/1
				X.	±0.30	X°	±5°			CHKD	DATE
				.X	±0.20	.X°	±2°	APPD	PRODUCT NAME	2.00mm Crimp Style Connectors	
				.XX	±0.08	.XX°	±1°	VIEW	PART. NO.	M2029R-xx-N0	
				.XXX	±0.03	.XXX°	±0.5°			UNITS	mm
				MODIFICATION		DATE			SCALE	1:1	
										DWG NO.	009