





环保物料


TEL:0769-82001899



SECTION A-A



SECTION B-B



SECTION C-C

SPECIFICATIONS

- 1.Voltage rating: 250V AC, DC
- 2.Current rating: 3A, AC, DC
- 3.Withstanding Voltage: 1000V AC/minute
- 4.Insulation resistance:800MΩ min
- 5.Temperature range: -25 °C-+85 °C
- 6.Contact resistance: 20mΩ max

TERMINAL

Material:Phosphor Bronze

Finish: Plated Tin or Plated Gold

Applicable wire: AWG#22-#28

Used in :P2029 SERIES HOUSING

Qty/Reel: 12000PCS

Part No.: T2029PS-2

00=镀金 2=镀锡

				TOLERANCE UNLESS OTHERWISE		DRAWN	CK tan	XFCN兴飞连接器有限公司 CONNECTORS XFCN CONNECTORS CO., LTD.		SHEET	1/1
				X. ±0.30	X° ±5°	CHKD				DATE	2010. 4. 12
				. X ±0.20	. X° ±2°	APPD		PRODUCT NAME	2.00mm Crimp Style Connectors	UNITS	mm
A0				. XX ±0.08	. XX° ±1°	VIEW				SCALE	1:1
VER	MODIFICATION	DRAW	DATE	. XXX ±0.03	. XXX° ±0.5°			PART. NO.	T2029PS-2	DWG NO.	009