


NOTES:
Rated Current: 3A
Rated Voltage: 250V AC/DC
Contact Resistance: 20mΩ max
Withstand Voltage: 1000V AC/Minute
Insulation Resistance: 1000MΩ min
Operation Temperature: -40℃ to +105℃
Material: PA66 UL94V-0






Ordering Information

WF2505 - H XX X 0 1

No. of pins
02P~15P

Color
E=Beige
W=White
B=Black
N=Brown

Packing
0=PE Bag



Dimensional & Ordering Information

Circuit	Part No.	Dimension	
		A	B
02	WF2505-H02X01	2.50	5.95
03	WF2505-H03X01	5.00	8.45
04	WF2505-H04X01	7.50	10.95
05	WF2505-H05X01	10.00	13.45
06	WF2505-H06X01	12.50	15.95
07	WF2505-H07X01	15.00	18.45
08	WF2505-H08X01	17.50	20.95
09	WF2505-H09X01	20.00	23.45
10	WF2505-H10X01	22.50	25.95
11	WF2505-H11X01	25.00	28.45
12	WF2505-H12X01	27.50	30.95
13	WF2505-H13X01	30.00	33.45
14	WF2505-H14X01	32.50	35.95
15	WF2505-H15X01	35.00	38.45

				OPERATION		DRAW Ding	DATE 2019/05/03	SCALE	FIT	PART NO. SEE TABLE	WCON Http: www.wcon.com WCON-Dongguan Tel: +86 769 85358920 Fax: +86 769 85358915 E-mail: sales@wcon.com WCON-Kunshan Tel: +86 512 57468408 Fax: +86 512 57468468 E-mail: salesks@wcon.com	
				X.X	±0.40			UNIT	mm			
A1	2019/05/03	Add the drawing	——	X.XX	±0.25	CHECK	DATE	SIZE	A4			
AO	2018/10/24	NEW	——	X.XXX	±0.15			SHEET	1/1			
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	Angle DIM	± 3' TOL	APPROVE	DATE	PROJ.		Customer NO.		