

HSF

NOTES:

Rated Current:3.0A

Contact Resistance:20mΩ max

Withstand Voltage:1000V AC/Minute

Insulation Resistance:1000MΩ min

Operation Temperature:-25℃ to+85℃



Insulator Material:PBT+30%G.F UL94V-0

Used with:WF2547-T

Mated with:WF2547-Wafer

Ordering Information

WF2547 - 2 H XX X 0 1

No. of pins
02P-20PColor
E=Beige
W=White
B=Black
U=BluePacking
0=PE Bag

Dimensional & Ordering Information:

Circuit	Part No.	Dimension	
		A	B
2x02	WF2547-2H02X01	2.54	5.08
2x03	WF2547-2H03X01	5.08	7.62
2x04	WF2547-2H04X01	7.62	10.16
2x05	WF2547-2H05X01	10.16	12.70
2x06	WF2547-2H06X01	12.70	15.24
2x07	WF2547-2H07X01	15.24	17.78
2x08	WF2547-2H08X01	17.78	20.32
2x09	WF2547-2H09X01	20.32	22.86
2x10	WF2547-2H10X01	22.86	25.40
2x12	WF2547-2H12X01	27.94	30.48
2x15	WF2547-2H15X01	35.56	38.10
2x18	WF2547-2H18X01	43.18	45.72
2x20	WF2547-2H20X01	48.26	50.80

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION		DRAW JYHuang	DATE 2013/11/14	SCALE UNIT	FIT mm inch	PART NO. SEE TAB	TITLE: 2.54 Housing Dual Row "T"Type	Customer NO.
				X.X	±0.40							
A1	2013/11/14	Add 2X02P Information		X.XX	±0.25	CHECK	DATE	SIZE	A4			
AO	2012/09/28	NEW		X.XXX	±0.15			SHEET	1/1			
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	Angle DIM	± 3° TOL	APPROVE	DATE	PROJ.				

WCON

Http: www.wcon.com

WCON-Dongguan WCON-Kunshan
Tel: +86 769 85358920 Tel: +86 512 57468408
Fax: +86 769 85358915 Fax: +86 512 57468468
E-mail: sales@wcon.com E-mail: salesks@wcon.com