

HSF

NOTES:

Current Rating: 5.0 AMP

Voltage Rating: 250V AC/DC

Temperature Range: -25°C to +85°C

Contact Resistance: 10mΩ Max.

Insulation Resistance: 1000MΩ Min.

Withstanding Voltage: 1000V AC/Minute

Material: PA66(UL94V-0)

Color: Black


Ordering Information

WF3001-1H XX B 01

Terminal Shape
H:HOUSING

No.of Pins
02-12P

Colour:
B:Black



CIRCUIT	Part No.	A	B
1X2	WF3001-1H02B01	NA	3.00[0.118]
1X3	WF3001-1H03B01	9.85[0.388]	6.00[0.236]
1X4	WF3001-1H04B01	12.85[0.506]	9.00[0.354]
1X5	WF3001-1H05B01	15.85[0.624]	12.00[0.472]
1X6	WF3001-1H06B01	18.85[0.742]	15.00[0.591]
1X7	WF3001-1H07B01	21.85[0.860]	18.00[0.709]
1X8	WF3001-1H08B01	24.85[0.978]	21.00[0.827]
1X9	WF3001-1H09B01	27.85[1.096]	24.00[0.945]
1X10	WF3001-1H10B01	30.85[1.215]	27.00[1.063]
1X11	WF3001-1H11B01	33.85[1.333]	30.00[1.181]
1X12	WF3001-1H12B01	36.85[1.451]	33.00[1.299]

				OPERATION		DRAW JYHuang	DATE 2013/05/15	SCALE	FIT	PART NO. WF3001-1HXXB01	WCON Http: www.wcon.com WCON-Dongguan Tel: +86 769 85358920 Fax: +86 769 85358915 E-mail: sales@wcon.com WCON-Kunshan Tel: +86 512 57468408 Fax: +86 512 57468468 E-mail: salesks@wcon.com
				X.X	±0.40		CHECK	DATE	UNIT		
				X.XX	±0.25	APPROVE	DATE	SIZE	A4	Customer NO.	
				X.XXX	±0.15			SHEET	1/1		
A0	2013/05/15	NEW	-----	Angle	± 3'			SHEET	1/1		
REV	DATE	MODIFICATION	DESCRIPTION	CHANGE	DIM	TOL		PROJ.			