



HSF

NOTES:

Current Rating:5.0A AMP
 Contact Resistance:10milliohm Max
 Withstand Voltage:1000V AC/Minute
 Insulation Resistance:1000Megohm Min
 Operation Temperature:-25°C to +85°C

Housing Material:LCP+30%GF(UL94V-0)
 Contact Material:Copper alloy
 Contact plating:Au/Sn over Ni Plating

RECOMMENDED PCB LAYOUT
 TOLERANCE IS ±0.05





Ordering Information

WF3001-1 WZ XX B X 3

Terminal shape:
WZ:Wafer 90° SMT

NO.of Pins
02~12Pin

Packing:
0=PE Bag
T=Tube
A=Tray
R=Tape&Reel



Circuit	A	B	C
02	9.65[0.380]	3.00[0.118]	14.20[0.559]
03	12.65[0.498]	6.00[0.236]	17.20[0.677]
04	15.65[0.616]	9.00[0.355]	20.20[0.795]
05	18.65[0.735]	12.00[0.473]	23.20[0.913]
06	21.65[0.853]	15.00[0.591]	26.20[1.031]
07	24.65[0.971]	18.00[0.709]	29.20[1.150]
08	27.65[1.089]	21.00[0.827]	32.20[1.268]
09	30.65[1.207]	24.00[0.945]	35.20[1.386]
10	33.65[1.325]	27.00[1.063]	38.20[1.504]
11	36.65[1.443]	30.00[1.181]	41.20[1.622]
12	39.65[1.561]	33.00[1.299]	44.20[1.740]

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION		DRAW FZY	DATE	SCALE	1:1	PART NO.
				Angle	± 3'					
A1	2012.05.03	料号由WF3001-1WZHXXBX3变更为WF3001-1WZXXBX3		X.X	±0.40	CHECK	2015.05.02	UNIT	mm	△ WF3001-1WZXXBX3
A0	2011.12.20	NEW	-	X.XX	±0.25	APPROVE		SIZE	A4	
				X.XXX	±0.15			SHEET	1/1	TITLE:
				DIM	TOL			PROJ.	Customer NO.	

WCON
 Http: www.wcon.com

WCON-Dongguan Tel: +86 769 85358920
 Fax: +86 769 85358915
 E-mail: sales@wcon.com

WCON-Kunshan Tel: +86 512 57468408
 Fax: +86 512 57468468
 E-mail: salesks@wcon.com