




# HSF

### NOTES:

Rated Current: 1.5AMP  
 Contact Resistance: 20mΩ max  
 Withstand Voltage: 250V AC/DC  
 Insulation Resistance: 1000MΩ min  
 Operation Temperature: -25°C to +85°C


Contact Material: Brass  
 Contact plating: Au Or Sn Over Ni  
 Insulator Material: PA66 UL94V-0



## Ordering Information

### WF2002B - WS XX X T 1

- No of pins 10-28P  
 Contact Plating S0=Gold Flash/Tin  
 Color B=Black W=White E=Beige  
 Packing T=Tube  
 S0=Gold Flash  
 S3=10u"Gold/Tin  
 S4=15u"Gold/Tin  
 S5=30u"Gold/Tin  
 G0=Gold Flash  
 G3=10u"Gold  
 G4=15u"Gold  
 G5=30u"Gold  
 Blank=Tin



### Specification & Ordering Information:

Circuit	Part No.	Dimension		
		A	B	C
10	WF2002B-WS10XT1	8.00	10.60	12.00
12	WF2002B-WS12XT1	10.00	12.60	14.00
14	WF2002B-WS14XT1	12.00	14.60	16.00
16	WF2002B-WS16XT1	14.00	16.60	18.00
18	WF2002B-WS18XT1	16.00	18.60	20.00
20	WF2002B-WS20XT1	18.00	20.60	22.00
22	WF2002B-WS22XT1	20.00	22.60	24.00
24	WF2002B-WS24XT1	22.00	24.60	26.00
26	WF2002B-WS26XT1	24.00	26.60	28.00
28	WF2002B-WS28XT1	26.00	28.60	30.00

OPERATION	DRAW	DATE	SCALE	FIT	PART NO.
X.X	JYHuang	2012/08/25	mm	SEE TAB	
X.XX	CHECK	DATE	UNIT	SIZE	TITLE:
X.XXX	APPROVE	DATE	mm	A4	PHD2.0 WAFER 180°
Angle	PROJ.	DATE	mm	1/1	Customer NO.
± 3'					

CHANGE	DIM	TOL

REV	DATE	MODIFICATION DESCRIPTION
A0	2012/08/25	NEW

# WCON

Http: www.wcon.com

WCON-Dongguan

WCON-Kunshan

Tel: +86 769 85358920 Tel: +86 512 57468408  
 Fax: +86 769 85358915 Fax: +86 512 57468468  
 E-mail: sales@wcon.com E-mail: sales@wcon.com