



Temperature	-20~70 C
Rated Load	DC 30V 0.3A
Contact Resistance	<0.03Ω
Insulation Resistance	>100MΩ
Withstand Voltage	AC500V(50Hz)/min
Actuating Force	2.2~30N
Life	3000次

PIN	PJ-305-X	
Schematic		G:Green R:Red

	MATERIAL	PLATING
terminal 1	Brass	ag
terminal 2	Phosphor Bronze	ag
terminal 3	Phosphor Bronze	ag
terminal 4	Phosphor Bronze	ag
terminal 5	Phosphor Bronze	ag
plastic	Pbt	

							DSND		DATE		SCALE: N/A	MODEL TYPE: 3.5 PHONE JACK		
					ANGLAR	±5°	DWN		DATE		VIEW: 	PART NO.: PJ-305-X		
Δx					X.X	±0.2mm	CHKD		DATE		UNIT: mm	DWG NO.: PJ-305-X		
Δx					X.XX	±0.1mm								
Δx					X.XXX	±0.05mm	APPD		DATE		SIZE: A4			
MARK	DESCRIPTION				DATE	REVISED						APPROVED		
REVISIONS							UNSPECIFIED TOLERANCES					XKB INDUSTRIAL PRECISION CO.,LIMITED		
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn												WEIGHT 1.0g	SHEET 1/1	REVISION A0