

A

B

C

D

E

F

A





B

C

D

E

F



PCB LAYOUT

- Specifications :
- Voltage rating: 250V AC / DC
 - Current rating: 3A AC / DC
 - Withstanding voltage: 800V AC/minute
 - Temperature range: -25°C~+85°C
 - Insulation resistance: ≥1000MΩ
 - Contact resistance: ≤10mΩ
 - After environmental testing: ≤20mΩ

X2015 W V-2*XX-N0 SN
① ② ③ ④ ⑤ ⑥

- ① Series No.
- ② Category: W-WAFER
- ③ Welding Board Angle: V-Straight 180°
- ④ Row No.-Pin No.: 2*XX-2*02P-2*20P
- ⑤ Material: N0-PA66 94V-0
- ⑥ Plating Category: SN-Bright Tin Plating;

Poles	Dimensions (mm)			Poles	Dimensions (mm)			Poles	Dimensions (mm)		
	A	B			A	B			A	B	
2*02	2.00	6.00		2*09	16.00	20.00		2*16	30.00	34.00	
2*03	4.00	8.00		2*10	18.00	22.00		2*17	32.00	36.00	
2*04	6.00	10.00		2*11	20.00	24.00		2*18	34.00	38.00	
2*05	8.00	12.00		2*12	22.00	26.00		2*19	36.00	40.00	
2*06	10.00	14.00		2*13	24.00	28.00		2*20	38.00	42.00	
2*07	12.00	16.00		2*14	26.00	30.00					
2*08	14.00	18.00		2*15	28.00	32.00					

X2015WV-2*XX-N0SN	PA66 UL 94V-0	Brass	Tin-Plated	X2015H
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Terminal

For and on behalf of
XKB INDUSTRIAL PRECISION CO., LIMITED
香港星坤工業精密有限公司

△ X					ANGULAR	±5°
△ X					L ≤ 4	±0.2
△ X					4 < L ≤ 16	±0.3
△ X					16 < L ≤ 63	±0.4
MARK					L > 63	±0.5
REVISIONS						
UNSPECIFIED TOLERANCES						

DSND		DATE		SCALE: N/A	MODEL TYPE: X2015WV-2*XX-N0SN
DWN		DATE		VIEW:	PART NO.:
CHKD		DATE		UNIT: mm	2.00 mm Crimp Style Connectors
APPD		DATE		SIZE: A4	DWG NO.:
XKB INDUSTRIAL PRECISION CO., LIMITED					WEIGHT 1.0g
					SHEET 1/1
					REVISION A0