

HSF

NOTES:

Current Rating: 5.0 AMP

Voltage Rating: 250V AC/DC

Temperature Range: -25°C to +85°C

Contact Resistance: 10mΩ Max.

Insulation Resistance: 1000MΩ Min.

Withstanding Voltage: 1000V AC/Minute

Material: PA66(UL94V-0)

Color: Black


Ordering Information

WF3001-1H XX B 01

Terminal Shape
H:HOUSING

No.of Pins
02-12P

Colour:
B:Black



SECTION: A-A

				OPERATION	DRAW	DATE	SCALE	FIT	PART NO.	WCON Http: www.wcon.com	
				X.X ±0.40	JYHuang	2013/05/15	UNIT	mm	WF3001-1HXXB01		
				X.XX ±0.25	CHECK	DATE	SIZE	A4	TITLE:	WCON-Dongguan Tel: +86 769 85358920 Fax: +86 769 85358915 E-mail: sales@wcon.com	
				X.XXX ±0.15			SHEET	1/1	3.00 mm SINGLE ROW HOUSING		
				Angle ± 3'	APPROVE	DATE	PROJ.		Customer NO.	WCON-Kunshan Tel: +86 512 57468408 Fax: +86 512 57468468 E-mail: salesks@wcon.com	
				DIM TOL							
AO	2013/05/15	NEW		-----							
REV	DATE	MODIFICATION DESCRIPTION		CHANGE							